



Standard



Microscope-mounting

Work Chambers

FEATURES

- **Standard or microscope-mounting arrangements**
- **Screened bottom to contain spent particles**
- **Drop-down front panel for larger parts**
- **Internal illumination (standard unit)**

These chambers are designed for hand held work. Using a tempered safety glass top, fluorescent internal illumination, screened bottom, and conveniently sized port holes allow for easy access.

The enameled steel can be used with either laboratory or production models and should be connected to a recommended dust collector. Microscope-mounting work chamber is for use with 10X to 40X scopes.

SPECIFICATIONS

Voltage:	110 volt, 60Hz or 220V, 50Hz (Standard unit)
Dimensions:	24”L x 15”D x 13.5”H (Standard unit) 19”L x 12”D x 9”H (Microscope-mounting)
Weight:	52 LB

Airbrasive, a Division of S.S. White Technologies

151 Old New Brunswick Road, Piscataway, NJ 08854 ph 800-779-4483 www.airbrasive.com